



EVN011



### Remote Control Dimmer universal 300W

#### Technical Features

##### Voltage

|                                          |             |
|------------------------------------------|-------------|
| Operating voltage                        | 230 - 230 V |
| Rated operational voltage U <sub>e</sub> | 230 - 230 V |

##### Connectivity

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Materials

|          |         |
|----------|---------|
| Colour   | Grey    |
| RAL code | 7035    |
| Material | Plastic |

##### Dimensions

|        |          |
|--------|----------|
| Height | 90 mm    |
| Width  | 17.50 mm |
| Depth  | 65 mm    |

##### Architecture

|                           |                    |
|---------------------------|--------------------|
| Control/operation element | Single push button |
|---------------------------|--------------------|

##### Power

|                                     |             |
|-------------------------------------|-------------|
| Power consumption during operation  | 2.10 VA     |
| Power consumption standby           | 0.2 W       |
| 230 V incandescent and halogen lamp | 300 W       |
| Power incandescent lamp             | 300 - 300 W |

##### Lighting

|                         |           |
|-------------------------|-----------|
| Dimmable 230 V LED lamp | 60 - 60 W |
| LED lamp power          | 60 W      |

##### Use conditions

|                       |              |
|-----------------------|--------------|
| Operating temperature | -10 - +45 °C |
|-----------------------|--------------|

##### Connection

|                                  |                         |
|----------------------------------|-------------------------|
| Cross-section rigid conductor    | 1.5 - 6 mm <sup>2</sup> |
| Cross-section flexible conductor | 1.5 - 6 mm <sup>2</sup> |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Texts

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Dimming principle  | Automatic load detection                              |
| Fuse               | With electronic short-circuit and overload protection |
| Installation mode  | For mounting on DIN rail                              |
| Type of connection | With screw terminals                                  |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|