



TRM600



### Control for latching relay, timer KNX radio

#### Technical Features

##### Connectivity

|                |           |
|----------------|-----------|
| Radio protocol | KNX Radio |
|----------------|-----------|

##### Settings

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

##### Connectivity

|                           |     |
|---------------------------|-----|
| Receiver category         | 2   |
| With bus system KNX       | No  |
| With bus system KNX radio | Yes |

##### Dimensions

|                |            |
|----------------|------------|
| Dimensions     | 18 x 40 mm |
| Height         | 18 mm      |
| Width          | 40 mm      |
| Depth          | 18 mm      |
| Built-in depth | 20 mm      |

##### Electric current

|               |        |
|---------------|--------|
| Rated current | 0.50 A |
|---------------|--------|

##### Materials

|        |            |
|--------|------------|
| Colour | Light grey |
|--------|------------|

##### Equipment

|                               |     |
|-------------------------------|-----|
| Radio frequency bidirectional | Yes |
| With switch for manual switch | Yes |

##### Frequency

|                           |                     |
|---------------------------|---------------------|
| Frequency                 | 50 - 60 Hz          |
| Radio reception frequency | 868.30 - 868.30 MHz |

##### Power

|              |       |
|--------------|-------|
| Output power | 115 W |
|--------------|-------|

##### Voltage

|                              |             |
|------------------------------|-------------|
| Operating voltage            | 230 - 230 V |
| Rated operational voltage Ue | 230 - 230 V |
| System supply voltage        | 230 V AC    |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -15 - 45 °C |
|-----------------------|-------------|

##### Connection

|                                  |                           |
|----------------------------------|---------------------------|
| Cross-section rigid conductor    | 0.5 - 2.5 mm <sup>2</sup> |
| Cross-section flexible conductor | 0.5 - 1.5 mm <sup>2</sup> |

##### Texts

|                    |  |
|--------------------|--|
| Function           | Pulse function only<br>Reset function (to factory setting) |
| Installation mode  | For installation behind flush-mounted inserts              |
| Type of connection | With screw-in lift terminals                               |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|