



SPN408D

SPD 4P pluggable 8kA class 2 with indicator

Technical Features

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage U_e	230 - 400 V
Continuous operating voltage U_c according to IEC 61643-1	255 V
Voltage protection level U_p according to IEC 61643-1	1.50 kV
Voltage protection level U_p L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level U_p L-N/PEN IEC 61643-11	1000 V
Type voltage supply	AC

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	2 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I_{max}) L-N(PEN)/ N-PE	8 kA

Dimensions

Height	90 mm
Width	72 mm
Depth	64 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	5 - 5 Nm
---------------------------	----------