



SPN440D

**SPD 4P pluggable 40kA class 2 with end of life indicator**

**Technical Features**

**Capacity**

Number of modules	4
-------------------	---

**Voltage**

Rated operational voltage $U_e$	240 - 415 V
Continuous operating voltage $U_c$ according to IEC 61643-1	275 V
Voltage protection level $U_p$ according to IEC 61643-1	1.20 kV
Voltage protection level $U_p$ L-PE/N-PE according to IEC 61643-11	1.6 kV

**Electric current**

Nominal discharge current $I_n$ 8 - 20 $\mu$ s L-N(PEN)/N-PE IEC 61643	15 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	40 kA

**Dimensions**

Height	98.7 mm
Width	71 mm
Depth	58.2 mm

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN-S TT
--------------	------------

**Equipment**

With remote signalling contact	No
--------------------------------	----

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------