



SPN440D

SPD 4P pluggable 40kA class 2 with end of life indicator

Technical Features

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	275 V
Voltage protection level Up according to IEC 61643-1	1.20 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.6 kV
Type voltage supply	AC

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	15 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (Imax) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	98.7 mm
Width	71 mm
Depth	58.2 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------