



EZF100



OFF Delay with control input time relay 24-240V AC/DC

Technical Features

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -25 - 55 °C |
| Storage/transport temperature | -25 - 70 °C |

Connection

| | |
|----------------------------------|---------------------------|
| Cross-section flexible conductor | 0.5 - 2.5 mm ² |
| Cross-section rigid conductor | 0.5 - 2.5 mm ² |
| Number of contacts | 1 |
| Type of contacts | 1x changeover |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Dimensions

| | |
|--------|----------|
| Height | 87 mm |
| Width | 17.50 mm |
| Depth | 65 mm |

Electric current

| | |
|-------------------------------|-----|
| Acceptable current rating AC1 | 8 A |
|-------------------------------|-----|

Equipment

| | |
|-----------------------|-----|
| Number of NC contacts | 0 |
| Number of NO contacts | 1 |
| Switch off delay | Yes |
| Switch on delay | No |

Settings

| | |
|------------|---------------|
| Time delay | 50 ms - 100 h |
|------------|---------------|

Voltage

| | |
|---------------------------|------------|
| Command voltage for 50 Hz | 24 - 240 V |
| Command voltage for 60 Hz | 24 - 240 V |
| Command voltage Us for DC | 24 - 240 V |
| Type voltage supply | AC/DC |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |