



WNA020B



**Cubyko LT push-button 1F composable white IP55**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Rocker
---------------------------	--------

**Materials**

Colour	Polar white
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Backside internal	Matt

**Dimensions**

Height	70 mm
Width	70 mm
Depth	45 mm
Built-in depth flush-mounted boxes	40 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Indicator lamp	Without
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Connectivity**

Type of connection	quickconnect
--------------------	--------------

**Connection**

Connector/plug type	Turn screw lock
---------------------	-----------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Texts**

Installation mode	For screw fastening
Switch mode	Change-over
Type of connection	With plug-in terminals

**Suitable for**

cubyko	
--------	--

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes