Product Datasheet
WBHSA2-MW



WBHSA2-MW

Allure Architrave 2 gang MW

Technical Features

Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Frequency	
Frequency	50 - 50 Hz
Materials	
Colour	White
Identification	
Assembly arrangement	Basic element with full cover plate
Connectivity	
Mounting type	Screw mounting
Controls and indicators	
Number of buttons	2
Electric current	
Rated current IN	16 A
Texts	
Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Push button	No
Sustainability	
Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes