



SPA401

SPD 4P monobloc 12.5kA class 1 with light indicator TT + TNS

Technical Features

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage Ue	230 - 400 V
Continuous operating voltage Uc according to IEC 61643-1	255 V
Voltage protection level Up according to IEC 61643-1	1.50 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level Up L-N/PEN IEC 61643-11	1500 V

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	12.5 kA
Max. overcurrent protection device, parallel connection (fuse)	160 A
Max. discharge (Imax) L-N(PEN)/ N-PE	12.5 kA

Dimensions

Height	90 mm
Width	144 mm
Depth	68 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T1
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	4 - 4 Nm
---------------------------	----------