



LS201

**Fuse carrier 1P 32A 415V BS88 1M**

**Technical Features**

**Dimensions**

Height	83 mm
Width	18 mm
Depth	75 mm

**Architecture**

Number of poles	1
Type of pole	1P

**Electric current**

Rated current	32 A
Rated current of fuse cartridge	2 A 4 A 6 A 8 A 10 A 16 A 20 A 25 A 32 A

**Capacity**

Number of modules	1
-------------------	---

**Installation, mounting**

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	3.63 W
---------------------------	--------

**Voltage**

Type voltage supply	AC/DC
---------------------	-------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	0.75 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

**Cover, door**

Interlockable	No
---------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes