



SPB215D

### Surge Protection Device 2P T2 TNS/TT U<sub>c</sub> 275V I<sub>n</sub> 5kA I<sub>max</sub> 15kA

#### Technical Features

##### Capacity

Number of modules	2
-------------------	---

##### Voltage

Rated operational voltage U <sub>e</sub>	240 - 415 V
Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	275 V
Voltage protection level U <sub>p</sub> according to IEC 61643-1	1 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11	1.6 kV
Voltage level U <sub>p</sub> L-N/PEN IEC 61643-11	1000 V

##### Electric current

Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643	5 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	15 kA

##### Dimensions

Height	89.80 mm
Width	35.60 mm
Depth	58.20 mm

##### Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

##### Network configuration

Network type	TN-S TT
--------------	------------

##### Equipment

With remote signalling contact	No
--------------------------------	----

##### Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>

##### Standards

Requirement class IEC 61643	T2
-----------------------------	----

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes