



WBHP2S-MW

Allure Double GPO Matt White

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC) Thermoplastic
----------	-------------------------------------

Treatment	Varnished
-----------	-----------

Dimensions

Number of units	2
-----------------	---

Built-in depth flush-mounted boxes	18 mm
------------------------------------	-------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Mounting-/Connection Position	Horizontal
-------------------------------	------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

Impact resistance IK	IK08
----------------------	------

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With screw terminals
--------------------	----------------------

Suitable for

allure	
--------	--

Product Datasheet

WBHP2S-MW

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes