



SPB140R

**Surge Protection Device 1P T2 TNC Uc 275V In 20kA I<sub>max</sub> 40kA remote contact**

**Technical Features**

**Capacity**

Number of modules	1
-------------------	---

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 415 V
Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	275 V
Voltage protection level U <sub>p</sub> according to IEC 61643-1	1.35 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level U <sub>p</sub> L-N/PEN IEC 61643-11	1350 V
Type voltage supply	AC

**Electric current**

Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	40 kA

**Dimensions**

Height	96.8 mm
Width	17.6 mm
Depth	58.20 mm

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN TT
--------------	----------

**Equipment**

With remote signalling contact	Yes
--------------------------------	-----

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes