



LR604

Fuse carrier 3P+N 50A 690V L51 6M

Technical Features

Dimensions

Height	107 mm
Width	105 mm
Depth	93 mm

Architecture

Number of poles	4
Type of pole	3P+N

Electric current

Rated current	50 A
Rated current of fuse cartridge	16 A 20 A 25 A 32 A 40 A 50 A 63 A 80 A 100 A 125 A

Capacity

Number of modules	6
-------------------	---

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	3.5 - 3.5 Nm
Mounting on	DIN rail

Power

Total power loss under I _N	20.60 W
---------------------------------------	---------

Voltage

Rated insulation voltage U _i	690 V
Rated impulse withstand voltage U _{imp}	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	2.5 - 25 mm ²
Cross-section of input and output with screws, for massive conductors	2.5 - 35 mm ²

Fuse

Fuse size	14 x 51
-----------	---------

Cover, door

Interlockable	No
---------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes