



LR601

**Fuse carrier 1P 50A 690V L51 1.5M**

**Technical Features**

**Dimensions**

Height	107 mm
Width	26.25 mm
Depth	93 mm

**Architecture**

Number of poles	1
-----------------	---

**Electric current**

Rated current	50 A
Rated current of fuse cartridge	2 A 4 A 6 A 8 A 10 A 12 A 16 A 20 A 25 A 32 A 40 A 50 A

**Capacity**

Number of modules	1.50
-------------------	------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Installation, mounting**

Nominal tightening torque	3.5 - 3.5 Nm
Mounting on	DIN rail

**Power**

Total power loss under I <sub>N</sub>	6 W
---------------------------------------	-----

**Voltage**

Rated insulation voltage U <sub>i</sub>	690 V
Rated impulse withstand voltage U <sub>imp</sub>	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	2.5 - 25 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	2.5 - 35 mm <sup>2</sup>

**Fuse**

Fuse size	14 x 51
-----------	---------

**Cover, door**

Interlockable	No
---------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes