



SPB365R

### Surge Protection Device 3P T2 TNC Uc 320V In 20kA Imax 65kA remote contact

#### Technical Features

##### Capacity

Number of modules	3
-------------------	---

##### Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	320 V
Voltage protection level Up according to IEC 61643-1	1.45 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.70 kV
Voltage level Up L-N/PEN IEC 61643-11	1450 V

##### Electric current

Nominal discharge current In 8 - 20 $\mu$ s L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	160 A
Max. discharge (Imax) L-N(PEN)/ N-PE	65 kA

##### Dimensions

Height	98.7 mm
Width	53.40 mm
Depth	70 mm

##### Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

##### Network configuration

Network type	TN-C
--------------	------

##### Equipment

With remote signalling contact	Yes
--------------------------------	-----

##### Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>
Cross-section signal contact	0.14 - 1.5 mm <sup>2</sup>

##### Standards

Requirement class IEC 61643	T2
-----------------------------	----

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes