



SPB340R

**Surge Protection Device 3P T2 TNC Uc 275V In 20kA Imax 40kA remote contact**

**Technical Features**

**Capacity**

Number of modules	3
-------------------	---

**Voltage**

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	275 V
Voltage protection level Up according to IEC 61643-1	1.35 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level Up L-N/PEN IEC 61643-11	1350 V

**Electric current**

Nominal discharge current In 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	250 A
Max. discharge (Imax) L-N(PEN)/ N-PE	40 kA

**Dimensions**

Height	98.7 mm
Width	53.40 mm
Depth	65.7 mm

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN-C TN TT
--------------	------------------

**Equipment**

With remote signalling contact	Yes
--------------------------------	-----

**Connection**

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>
Cross-section signal contact	0.14 - 1.5 mm <sup>2</sup>

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes