



SPA932

**SPD T1+T2 4P TN-S TT 50kA Up 1,2kV**

**Technical Features**

**Electric current**

Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
--------------------------------------	-------

**Network configuration**

Network type	TN-S TT
--------------	------------

**Electric current**

Max. overcurrent protection device, parallel connection (fuse)	160 A
--	-------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Electric current**

Lightning impulse current Iimp (10/350 µs) IEC 61643 L-N(PEN)/ N-PE	12.5 kA 50 kA
---	------------------

**Equipment**

With remote signalling contact	No
--------------------------------	----

**Capacity**

Number of modules	4
-------------------	---

**Voltage**

Voltage protection level Up according to IEC 61643-1	1.20 kV
Continuous operating voltage Uc according to IEC 61643-1	335 V
Rated operational voltage Ue	240 - 415 V
Voltage level Up L-N/PEN IEC 61643-11	1.2 kV

**Architecture**

Number of poles	4
-----------------	---

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Dimensions**

Height	89.80 mm
Width	71.20 mm
Depth	77.50 mm

**Controls and indicators**

With indicator lamp	Yes
---------------------	-----

**Standards**

Requirement class IEC 61643	T1 T2
-----------------------------	----------

**Installation, mounting**

Nominal tightening torque	3 - 4.5 Nm
---------------------------	------------

**Connection**

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>
Cross-section signal contact	0.4 - 1.5 mm <sup>2</sup>

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes