



AD106B

RCBO Electronic 1M 1P 10kA C-6A 30mA A Class

Technical Features

Architecture

Type of pole	1P
Curve	C

Electric current

Rated current	6 A
Rated residual operating current I _{dn}	30 mA
Rated current -25°C	7.72 A
Rated current at -20°C	7.58 A
Rated current -15°C	7.43 A
Rated current -10°C	7.29 A
Rated current -5°C	7.14 A
Rated current at 0°C	6.99 A
Rated current 5°C	6.83 A
Rated current 10°C	6.67 A
Rated current 15°C	6.51 A
Rated current at 20°C	6.35 A
Rated current 25°C	6.18 A
Rated current 30°C	6 A
Rated current 35°C	5.82 A
Rated current at 40°C	5.63 A
Rated current at 50°C	5.24 A
Rated current 55°C	5.03 A
Rated current 60°C	4.81 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	10 kA
-----------------------------------------------------------------------------------	-------

Voltage

Rated insulation voltage U _i	250 V
Rated impulse withstand voltage U _{imp}	4000 V
Max. operating voltage	253 V
Rated operational voltage U _e	230 - 240 V
Overvoltage category according to IEC 60947-1	3

Power

Total power loss under I _N	1.50 W
---------------------------------------	--------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Max. Altitude	2000 m
Class of energy limitation I ² t	3

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Connection

Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input with screws, for massive conductors	1 - 25 mm ²

Installation, mounting

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	115 mm
Width	17.50 mm
Depth	70 mm

Use conditions

Operating temperature	-5 - 60 °C
Storage/transport temperature	-25 - 60 °C

Connection

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²

Sustainability

RoHS conform	Yes
--------------	-----