



WBMDUR

Mechanism rotary dimmer trailing-edge

Technical Features

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|----------|--------------------|
| Colour | White |
| Material | Polycarbonate (PC) |

Dimensions

| | |
|--------|-------|
| Height | 24 mm |
| Width | 24 mm |
| Depth | 65 mm |

Architecture

| | |
|---------------------------|----------------------|
| Control/operation element | Push & rotary switch |
|---------------------------|----------------------|

Power

| | |
|---------------------------|--------|
| Power consumption standby | 0.10 W |
|---------------------------|--------|

Lighting

| | |
|-------------------------|-----------|
| Dimmable 230 V LED lamp | 3 - 250 W |
| LED lamp power | 250 W |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Texts

| | |
|-----------------------|--|
| Dimming principle | Phase cut-off |
| Fuse | Short-circuit and overload-proof (electronic fuse) |
| Installation mode | RotoLoc® |
| Type of connection | With screw terminals |
| Extension unit input | With extension unit input for slave push-button WBMESL |
| Operation and control | No Bluetooth interface |

Equipment

| | |
|------------------|-----|
| Substation input | Yes |
|------------------|-----|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |