
Product Datasheet
NRN132



NRN132

MCB 1P 20kA C-32A 1M

Technical Features

Electric current	
Rated current IN	32 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	7.50 kA
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	20 kA
Rated current at -15°C	38.3 A
Rated current at -10°C	37.6 A
Rated current at -5°C	36.9 A
Rated current at 0°C	36.2 A
Rated current at 5°C	35.5 A
Rated current at 10°C	34.8 A
Rated current at 15°C	34.1 A
Rated current at 20°C	33.4 A
Rated current at 25°C	32.7 A
Rated current at 30°C	32 A
Rated current at 35°C	31.2 A
Rated current at 40°C	30.4 A
Rated current at 45°C	29.59 A
Rated current at 50°C	28.79 A
Rated current at 55°C	27.99 A
Rated current at 60°C	27.19 A
Rated current at 65°C	26.38 A
Rated current at 70°C	25.58 A
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	20 kA

Architecture	
Type of pole	1P
Curve	C

Capacity	
Number of modules	1

Installation, mounting	
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage	
Rated operational voltage Ue	230 - 240 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

Frequency	
Frequency	50 - 60 Hz

Connection	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm^2
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for massive conductors	1 - 35 mm^2

Installation, mounting	
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety	
Ingress Protection (IP) class	IP20
Grid distance	60 mm

Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I^2t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C
Power	
Power dissipation at IN	3.65 W
Connectivity	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Dimensions	
Height	83 mm
Width	17.50 mm
Depth	70 mm
Endurance	
Electric endurance in number of cycles	4000
Sustainability	
RoHS conform	Yes