



## 20A Double Pole Switch Marked FREEZER

### Technical Features

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

### Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

### Connectivity

Mounting type	Screw mounting
---------------	----------------

### Controls and indicators

Number of buttons	1
-------------------	---

### Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	21.90 mm
----------------	----------

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Architecture

Control/operation element	Single rocker
---------------------------	---------------

### Electric current

Rated current	20 A
---------------	------

### Texts

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-pole
-------------	--------

### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----