




WBME5A



**Mechanism, 5A electronic push button**

**Technical Features**

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
Material	Polycarbonate (PC)

**Dimensions**

Built-in depth	45 mm
Depth	45 mm

**Architecture**

Control/operation element	Push button
---------------------------	-------------

**Power**

Power consumption standby	0.35 W
230 V incandescent and halogen lamp	1200 W

**Lighting**

LED lamp power	500 W
----------------	-------

**Use conditions**

Operating temperature	5 - 40 °C
-----------------------	-----------

**Connection**

Cross-section rigid conductor	1 - 2.5 mm <sup>2</sup>
-------------------------------	-------------------------

**Capacity**

Number of modules	1
-------------------	---

**Texts**

Installation mode	RotoLoc®
Type of connection	With screw terminals
Extension unit input	With extension unit input for slave push-button WBMESL

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes