



ARF925D

### RCBO with dangerous arc detection 25A B curve 6kA Type A 30mA

#### Technical Features

##### Electric current

Rated current	25 A
Rated current -25°C	31.88 A
Rated current at -20°C	31.28 A
Rated current -15°C	30.68 A
Rated current -10°C	30.15 A
Rated current -5°C	29.47 A
Rated current at 0°C	28.86 A
Rated current 5°C	28.26 A
Rated current 10°C	27.66 A
Rated current 15°C	27.05 A
Rated current at 20°C	26.45 A
Rated current 25°C	25.84 A
Rated current 30°C	25 A
Rated current 35°C	24.64 A
Rated current at 40°C	24.03 A
Rated current at 45°C	23.43 A
Rated current at 50°C	22.98 A
Rated current 55°C	22.22 A
Rated current 60°C	21.62 A
Rated current 65°C	21.01 A
Rated current 70°C	20.41 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 61009-1	6 kA

##### Architecture

Curve	B
Type of pole	1P+N

##### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

##### Electric current

Breaking and opening capacity I <sub>dm</sub>	6 kA
Rated residual operating current I <sub>dn</sub>	30 mA

##### Voltage

Rated insulation voltage U <sub>i</sub>	500 V
---	-------

##### Safety

Residual current type	A
-----------------------	---

##### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

##### Power

Total power loss under I <sub>N</sub>	7.95 W
---------------------------------------	--------

##### Use conditions

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

---

**Endurance**

Number of mechanical operations	4000
Electric endurance in number of cycles	2000

---

**Installation, mounting**

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

---

**Capacity**

Number of modules	3
-------------------	---

---

**Installation, mounting**

Type of bottom connection for modular devices	Screw terminal
Type of top connection for modular devices	Screw terminal

---

**Dimensions**

Height	83 mm
Width	53.20 mm
Depth	70 mm

---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

---

**Sustainability**

RoHS conform	Yes
--------------	-----