



ARF516D

RCBO with dangerous arc detection 16A B curve 10kA Type A 30mA

Technical Features

Electric current

Rated current	16 A
Rated current -25°C	19.92 A
Rated current at -20°C	19.60 A
Rated current -15°C	19.27 A
Rated current -10°C	18.93 A
Rated current -5°C	18.59 A
Rated current at 0°C	18.24 A
Rated current 5°C	17.89 A
Rated current 10°C	17.53 A
Rated current 15°C	17.16 A
Rated current at 20°C	16.78 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.59 A
Rated current at 40°C	15.18 A
Rated current at 45°C	14.75 A
Rated current at 50°C	14.31 A
Rated current 55°C	13.86 A
Rated current 60°C	13.39 A
Rated current 65°C	12.90 A
Rated current 70°C	12.39 A
Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 61009-1	10 kA

Architecture

Curve	B
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	10 kA
---	-------

Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

Electric current

Breaking and opening capacity I _{dm}	10 kA
Rated residual operating current I _{dn}	30 mA

Voltage

Rated insulation voltage U _i	500 V
---	-------

Safety

Residual current type	A
-----------------------	---

Voltage

Rated impulse withstand voltage U _{imp}	4000 V
Rated operational voltage U _e	230 - 230 V

Power

Total power loss under I _N	5.76 W
---------------------------------------	--------

Use conditions

Class of energy limitation I ² t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

Endurance

Number of mechanical operations	4000
---------------------------------	------

Endurance

Electric endurance in number of cycles	2000
--	------

Installation, mounting

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

Type of bottom connection for modular devices	Screw terminal
---	----------------

Type of top connection for modular devices	Screw terminal
--	----------------

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	83 mm
--------	-------

Width	53.20 mm
-------	----------

Depth	70 mm
-------	-------

Connection

Cross-section of output with screws, for flexible conductors	1 - 16 mm ²
--	------------------------

Cross-section of output with screws, for massive conductors	1 - 25 mm ²
---	------------------------

Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
---	------------------------

Cross-section of input with screws, for massive conductors	1 - 25 mm ²
--	------------------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Sustainability

RoHS conform	Yes
--------------	-----
