



ARC532U

MCB with dangerous arc detection 1P+N 10kA B-32A 2M

Technical Features

Electric current

Rated current	32 A
Rated current -25°C	38.30 A
Rated current at -20°C	37.77 A
Rated current -15°C	37.24 A
Rated current -10°C	36.69 A
Rated current -5°C	36.14 A
Rated current at 0°C	35.58 A
Rated current 5°C	35.01 A
Rated current 10°C	34.43 A
Rated current 15°C	33.84 A
Rated current at 20°C	33.24 A
Rated current 25°C	32.63 A
Rated current 30°C	32 A
Rated current 35°C	31.52 A
Rated current at 40°C	31.03 A
Rated current at 45°C	30.54 A
Rated current at 50°C	30.03 A
Rated current 55°C	29.52 A
Rated current 60°C	29 A
Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 60898-1	10 kA

Architecture

Curve	B
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	10 kA
---	-------

Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V
Rated operational voltage U _e	230 - 230 V

Power

Total power loss under I _N	8.31 W
---------------------------------------	--------

Use conditions

Class of energy limitation I ² t	3
---	---

Endurance

Number of mechanical operations	4000
Electric endurance in number of cycles	2000

Installation, mounting

Nominal tightening torque	2 - 2 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

Capacity

Number of modules	2
-------------------	---

Dimensions

Height	85 mm
Width	35.50 mm

Dimensions

Depth	70 mm
-------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 60 °C
Storage/transport temperature	-40 - 70 °C

Connection

Cross-section of output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of output with screws, for massive conductors	1.5 - 25.0 mm ²
Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input with screws, for massive conductors	1.5 - 25.0 mm ²

Sustainability

RoHS conform	Yes
--------------	-----
