



ARC590U

MCB with dangerous arc detection 1P+N 10kA C-40A 2M

Technical Features

Electric current

Rated current	40 A
Rated current -25°C	46.88 A
Rated current at -20°C	46.26 A
Rated current -15°C	45.63 A
Rated current -10°C	45.01 A
Rated current -5°C	44.38 A
Rated current at 0°C	43.76 A
Rated current 5°C	43.14 A
Rated current 10°C	42.51 A
Rated current 15°C	41.89 A
Rated current at 20°C	41.26 A
Rated current 25°C	40.64 A
Rated current 30°C	40 A
Rated current 35°C	39.40 A
Rated current at 40°C	38.78 A
Rated current at 45°C	38.16 A
Rated current at 50°C	37.53 A
Rated current 55°C	36.88 A
Rated current 60°C	36.23 A
Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 60898-1	10 kA

Architecture

Curve	C
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	10 kA
---	-------

Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V
Rated operational voltage U _e	230 - 230 V

Power

Total power loss under I _N	11.98 W
---------------------------------------	---------

Use conditions

Class of energy limitation I ² t	3
---	---

Endurance

Number of mechanical operations	4000
Electric endurance in number of cycles	2000

Installation, mounting

Nominal tightening torque	2 - 2 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

Capacity

Number of modules	2
-------------------	---

Dimensions

Height	85 mm
Width	35.50 mm

Dimensions

Depth	70 mm
-------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Storage/transport temperature	-40 - 70 °C
-------------------------------	-------------

Connection

Cross-section of output with screws, for flexible conductors	1 - 16 mm ²
--	------------------------

Cross-section of output with screws, for massive conductors	1.5 - 25.0 mm ²
---	----------------------------

Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
---	------------------------

Cross-section of input with screws, for massive conductors	1.5 - 25.0 mm ²
--	----------------------------

Sustainability

RoHS conform	Yes
--------------	-----
