



CNA684U

### RCCB 3P+N 100A 100mA A S

#### Technical Features

##### Architecture

Type of pole	3P+N
--------------	------

##### Electric current

Rated current	100 A
Rated residual operating current Idn	100 mA
Breaking and opening capacity Idm	1.25 kA
Rated conditional short-circuit current Irc according to EN61008-1	10 kA
Rated current -25°C	100 A
Rated current at -20°C	100 A
Rated current at -15°C	100 A
Rated current at -10°C	100 A
Rated current at -5°C	100 A
Rated current at 0°C	100 A
Rated current 5°C	100 A
Rated current 10°C	100 A
Rated current 15°C	100 A
Rated current at 20°C	100 A
Rated current 25°C	100 A
Rated current 30°C	100 A
Rated current 35°C	100 A
Rated current at 40°C	100 A
Rated current at 45°C	100 A
Rated current at 50°C	100 A
Rated current 55°C	100 A
Rated current 60°C	100 A
Rated current 65°C	95 A
Rated current 70°C	90 A

##### Installation, mounting

Nominal tightening torque top terminal	3.60 - 3.60 Nm
Nominal tightening torque down terminal	3.60 - 3.60 Nm

##### Voltage

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage Uimp	4000 V
Rated impulse withstand voltage Uimp IEC 60947-3	6000 V
Max. operating voltage	440 V

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Capacity

Number of modules	4
-------------------	---

##### Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

##### Safety

Residual current type	A SEL
Ingress Protection (IP) class	IP20

##### Installation, mounting

Type of bottom connection for modular devices	biconnect
Top removability	Yes

**Connection**

Cross-section of output with screws, for massive conductors	1 - 50 mm <sup>2</sup>
Cross-section of output with screws, for flexible conductors	1 - 35 mm <sup>2</sup>

**Power**

Total power loss under IN	21.48 W
---------------------------	---------

**Use conditions**

Max. Altitude	2000 m
Operating temperature	-25 - 60 °C

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	85 mm
Width	72 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----