



NRN420

**MCB 4P 25kA C-20A 4M**

**Technical Features**

**Electric current**

|   |       |
|---|-------|
| Rated current   | 20 A  |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2       | 15 kA |
| Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2     | 25 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2     | 50 kA |

**Architecture**

|              |    |
|--------------|----|
| Type of pole | 4P |
| Curve        | C  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

**Main electrical attributes**

|   |       |
|---|-------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 10 kA |
|---|-------|

**Installation, mounting**

|   |                |
|---|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

**Voltage**

|                                      |             |
|--------------------------------------|-------------|
| Rated operational voltage Ue         | 415 - 415 V |
| Type voltage supply                  | AC          |
| Rated insulation voltage Ui          | 500 V       |
| Rated impulse withstand voltage Uimp | 6000 V      |

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Connection**

|  |                        |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |

**Installation, mounting**

|   |                |
|---|----------------|
| Nominal tightening torque                     | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Use conditions**

|  |                  |
|--|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

**Power**

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 10.87 W |
|---------------------------|---------|

**Endurance**

|  |       |
|--|-------|
| Electric endurance in number of cycles | 4000  |
| Number of mechanical operations        | 20000 |

**Connectivity**

|   |                  |
|---|------------------|
| Type of connection                            | Screw terminal   |
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

**Dimensions**

|        |       |
|--------|-------|
| Height | 83 mm |
| Width  | 70 mm |
| Depth  | 70 mm |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

**Illustrations | Drawings**

