



NDN100A

**MCB 1P 10kA/15kA D-0.5A 1M**

**Technical Features**

**Electric current**

Rated current	0.50 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	15 kA
Rated current -25°C	0.74 A
Rated current at -20°C	0.72 A
Rated current -15°C	0.70 A
Rated current -10°C	0.68 A
Rated current -5°C	0.66 A
Rated current at 0°C	0.64 A
Rated current 5°C	0.63 A
Rated current 10°C	0.61 A
Rated current 15°C	0.59 A
Rated current at 20°C	0.57 A
Rated current 25°C	0.56 A
Rated current 30°C	0.50 A
Rated current 35°C	0.49 A
Rated current at 40°C	0.49 A
Rated current at 45°C	0.48 A
Rated current at 50°C	0.48 A
Rated current 55°C	0.46 A
Rated current 60°C	0.44 A
Rated current 65°C	0.42 A
Rated current 70°C	0.40 A

**Architecture**

Type of pole	1P
Curve	D

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

---

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	0.14 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	17.50 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----