Product Datasheet
MU350A



MU350A

MCB 3P 6kA C-50A 3M

Technical Features

Electric current	
Rated current IN	50 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	6 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated current at -15°C	60.97 A
Rated current at -10°C	59.75 A
Rated current at -5°C	58.53 A
Rated current at 0°C	57.31 A
Rated current at 5°C	56.09 A
Rated current at 10°C	54.88 A
Rated current at 15°C	53.66 A
Rated current at 20°C	52.44 A
Rated current at 25°C	51.22 A
Rated current at 30°C	50 A
Rated current at 35°C	48.4 A
Rated current at 40°C	46.8 A
Rated current at 45°C	45.2 A
Rated current at 50°C	43.6 A
Rated current at 55°C	42 A
Rated current at 60°C	40.4 A
Rated current at 65°C	38.8 A
Rated current at 70°C	37.2 A
Rated short-circuit breaking capacity Icn under 400 V AC according to IEC 60898-1	6 kA

Architecture	
Type of pole	3P
Curve	C

Capacity	
Number of modules	3

Main electrical attributes	
Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA

Installation, mounting	
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage	
Rated operational voltage Ue	400-400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency	
Frequency	50 - 60 Hz

Connection	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm^2
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for flexible conductors	1 - 25 mm^2
Cross-section of input with screws, for massive conductors	1 - 35 mm^2

Installation, mounting	
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety	
Ingress Protection (IP) class	IP20
Grid distance	60 mm
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I^2t	3
Operating temperature	-25 - 70 °C
Power	
Power dissipation at IN	15.4 W
Connectivity	
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Type of connection	Screw terminal
Dimensions	
Height	83 mm
Width	52.5 mm
Depth	70 mm
Endurance	
Electric endurance in number of cycles	4000
Sustainability	
RoHS conform	Yes