

**MCB 2P 6/10kA C-63A 2M**

**Technical Features**

**Electric current**

Rated current	63 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	6 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	6 kA
Rated current -15°C	78.1 A
Rated current -10°C	76.5 A
Rated current -5°C	75.1 A
Rated current at 0°C	73.5 A
Rated current 5°C	72 A
Rated current 10°C	70.5 A
Rated current 15°C	69 A
Rated current at 20°C	67.5 A
Rated current 25°C	66 A
Rated current 30°C	63 A
Rated current 35°C	62 A
Rated current at 40°C	60.5 A
Rated current at 45°C	58.7 A
Rated current at 50°C	58.3 A
Rated current 55°C	52.8 A
Rated current 60°C	50.5 A
Rated current 65°C	48.1 A
Rated current 70°C	45.6 A

**Architecture**

Type of pole	2P
Curve	C

**Capacity**

Number of modules	2
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	400-400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class

IP20

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2

2

Class of energy limitation I<sup>2</sup>t

3

Air humidity protection

For all climates

Operating temperature

-25 - 70 °C

**Power**

Total power loss under IN

13.1 W

**Connectivity**

Type of connection

Screw terminal

Top connection alignment for modular devices

Aligned terminal

Down connection alignment for modular devices

Aligned terminal

**Dimensions**

Height

83 mm

Width

35 mm

Depth

70 mm

**Sustainability**

RoHS conform

Yes