



MT163A

MCB 1P 6kA B-63A 1M

Technical Features

Electric current

| | |
|---|--------|
| Rated current | 63 A |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2 | 6 kA |
| Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1 | 6 kA |
| Rated current -15°C | 78.1 A |
| Rated current -10°C | 76.5 A |
| Rated current -5°C | 75.1 A |
| Rated current at 0°C | 73.5 A |
| Rated current 5°C | 72 A |
| Rated current 10°C | 70.5 A |
| Rated current 15°C | 69 A |
| Rated current at 20°C | 67.5 A |
| Rated current 25°C | 66 A |
| Rated current 30°C | 63 A |
| Rated current 35°C | 62 A |
| Rated current at 40°C | 60.5 A |
| Rated current at 45°C | 58.7 A |
| Rated current at 50°C | 58.3 A |
| Rated current 55°C | 52.8 A |
| Rated current 60°C | 50.5 A |
| Rated current 65°C | 48.1 A |
| Rated current 70°C | 45.6 A |

Architecture

| | |
|--------------|----|
| Type of pole | 1P |
| Curve | B |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical attributes

| | |
|---|------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 6 kA |
|---|------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

Voltage

| | |
|--------------------------------------|-----------|
| Rated operational voltage Ue | 230-400 V |
| Type voltage supply | AC |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP20 |
| Grid distance | 60 mm |

Use conditions

| | |
|--|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Air humidity protection | For all climates |
| Operating temperature | -25 - 70 °C |

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 5.73 W |
|---------------------------|--------|

Connectivity

| | |
|---|------------------|
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

Dimensions

| | |
|--------|---------|
| Height | 83 mm |
| Width | 17.5 mm |
| Depth | 70 mm |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|