



ALX433T



**RCBO Electronic 3M 3P+N 10kA D-32A 30mA A**

**Technical Features**

**Architecture**

Type of pole	3P+N
Curve	D

**Electric current**

Rated current	32 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -5°C	36.68 A
Rated current at 0°C	36.02 A
Rated current 5°C	35.42 A
Rated current 10°C	34.78 A
Rated current 15°C	34.15 A
Rated current at 20°C	33.45 A
Rated current 25°C	32.73 A
Rated current 30°C	32 A
Rated current 35°C	31.28 A
Rated current at 40°C	30.55 A
Rated current at 45°C	29.82 A
Rated current at 50°C	29.09 A
Rated current 55°C	28.36 A
Rated current 60°C	27.63 A
Min./max. threshold value of the AC thermal operation	1.13-1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4 kV
Rated operational voltage U <sub>e</sub>	400 - 415 V
Overvoltage category according to IEC 60947-1	3
Type voltage supply	AC
Dielectric strength value of power frequency	2 kV

**Power**

Total power loss under I <sub>N</sub>	14.17 W
---------------------------------------	---------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Use conditions**

Max. altitude	2000 m
---------------	--------

**Installation, mounting**

Nominal tightening torque down terminal	2.5 - 2.5 Nm
Nominal tightening torque top terminal	2.5 - 2.5 Nm

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
---	---

**Connection**

Cross-section of input with screws, for flexible conductors	1-16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1-25 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.5 - 2.5 Nm
---------------------------	--------------

**Capacity**

Number of modules	3
-------------------	---

---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

---

**Dimensions**

Height	84 mm
Width	54 mm
Depth	70 mm

---

**Use conditions**

Operating temperature	-5 - 70 °C
Storage/transport temperature	-25 - 70 °C

---

**Connection**

Cross-section of input and output with screws, for flexible conductors	1-16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1-25 mm <sup>2</sup>

---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

---

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes