



ARC525U

**MCB with dangerous arc detection 1P+N 10kA B-25A 2M**

**Technical Features**

**Electric current**

Rated current	25 A
Rated current -25°C	28.19 A
Rated current at -20°C	27.91 A
Rated current -15°C	27.64 A
Rated current -10°C	27.36 A
Rated current -5°C	27.07 A
Rated current at 0°C	26.79 A
Rated current 5°C	26.50 A
Rated current 10°C	26.21 A
Rated current 15°C	25.91 A
Rated current at 20°C	25.61 A
Rated current 25°C	25.31 A
Rated current 30°C	25 A
Rated current 35°C	24.76 A
Rated current at 40°C	24.52 A
Rated current at 45°C	24.27 A
Rated current at 50°C	24.02 A
Rated current 55°C	23.77 A
Rated current 60°C	23.52 A

**Architecture**

Curve	B
Type of pole	1P+N

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

**Power**

Total power loss under I <sub>N</sub>	6.48 W
---------------------------------------	--------

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 60 °C
Storage/transport temperature	-40 - 70 °C

**Endurance**

Number of mechanical operations	4000
Electric endurance in number of cycles	2000

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

**Capacity**

Number of modules	2
-------------------	---

**Dimensions**

Height	85 mm
--------	-------

---

**Dimensions**

Width	35.50 mm
Depth	70 mm

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----