



NBN240A

MCB 2P 10kA/15kA B-40A 2M

Technical Features

Electric current

Rated current	40 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	15 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated current -25°C	60.16 A
Rated current at -20°C	58.43 A
Rated current -15°C	56.70 A
Rated current -10°C	55.35 A
Rated current -5°C	53.24 A
Rated current at 0°C	51.51 A
Rated current 5°C	49.78 A
Rated current 10°C	48.06 A
Rated current 15°C	46.33 A
Rated current at 20°C	44.60 A
Rated current 25°C	42.87 A
Rated current 30°C	40 A
Rated current 35°C	39.41 A
Rated current at 40°C	37.69 A
Rated current at 45°C	35.96 A
Rated current at 50°C	34.99 A
Rated current 55°C	32.50 A
Rated current 60°C	30.77 A
Rated current 65°C	29.04 A
Rated current 70°C	27.31 A

Architecture

Type of pole	2P
Curve	B

Capacity

Number of modules	2
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for massive conductors	1 - 35 mm ²

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Class of energy limitation I ² t	3
---	---

Operating temperature	-25 - 70 °C
-----------------------	-------------

Power

Total power loss under IN	6.70 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	4000
--	------

Number of mechanical operations	20000
---------------------------------	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
--	------------------

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	83 mm
--------	-------

Width	35 mm
-------	-------

Depth	70 mm
-------	-------

Sustainability

RoHS conform	Yes
--------------	-----
