



NDN201A

**MCB 2P 10kA/15kA D-1A 2M**

**Technical Features**

**Electric current**

Rated current	1 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> AC IEC 60947-2	15 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	15 kA
Rated current -15°C	1.29 A
Rated current -10°C	1.26 A
Rated current -5°C	1.23 A
Rated current at 0°C	1.20 A
Rated current 5°C	1.17 A
Rated current 10°C	1.14 A
Rated current 15°C	1.10 A
Rated current at 20°C	1.07 A
Rated current 25°C	1.04 A
Rated current 30°C	1 A
Rated current 35°C	0.96 A
Rated current at 40°C	0.92 A
Rated current at 45°C	0.88 A
Rated current at 50°C	0.84 A
Rated current 55°C	0.80 A
Rated current 60°C	0.75 A
Rated current 65°C	0.70 A
Rated current 70°C	0.64 A

**Architecture**

Type of pole	2P
Curve	D

**Capacity**

Number of modules	2
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Nominal tightening torque	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

---

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	2.11 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	35 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----