



NDN363A

**MCB 3P 10kA/15kA D-63A 3M**

**Technical Features**

**Electric current**

Rated current	63 A
Rated current -15°C	76.06 A
Rated current -10°C	74.72 A
Rated current -5°C	73.36 A
Rated current at 0°C	71.97 A
Rated current 5°C	70.56 A
Rated current 10°C	69.11 A
Rated current 15°C	67.64 A
Rated current at 20°C	66.13 A
Rated current 25°C	64.58 A
Rated current 30°C	63 A
Rated current 35°C	60.96 A
Rated current at 40°C	58.86 A
Rated current at 45°C	56.68 A
Rated current at 50°C	54.40 A
Rated current 55°C	52.03 A
Rated current 60°C	49.55 A
Rated current 65°C	46.94 A
Rated current 70°C	44.17 A

**Architecture**

Type of pole	3P
Curve	D

**Capacity**

Number of modules	3
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	10 kA
---	-------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Nominal tightening torque	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

---

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	19.90 W
---------------------------	---------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	52.50 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----