



HWS2E420D1AE

**Air Circuit Breaker HWS2 66kA 2000A 4P Drawout LSI**

**Technical Features**

**Electric current**

Rated current	2000 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	66 kA
Rated service breaking capacity $I_{cs}$ under 230 V AC according to IEC 60947-2	66 kA
Rated service breaking capacity $I_{cs}$ under 400 V AC according to IEC 60947-2	66 kA

**Endurance**

Electric endurance in number of cycles	8000
Number of mechanical operations	12000

**Voltage**

Rated insulation voltage $U_i$	1000 V
Rated impulse withstand voltage $U_{imp}$	12 kV
Type voltage supply	AC

**Resistance**

Internal resistance	18.3 $\mu\Omega$
---------------------	------------------

**Architecture**

Number of poles	4
Number of protected poles	4
Device construction type	Drawout
Type of pole	4P

**Tripping**

Time of response when closing	40 ms
-------------------------------	-------

**Power**

Total power loss under $I_N$	273.4 W
------------------------------	---------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes