



NDN140A

MCB 1P 10kA/15kA D-40A 1M

Technical Features

Electric current

| | |
|---|-------|
| Rated current | 40 A |
| Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity I _{cu} AC IEC 60947-2 | 15 kA |
| Rated current 30°C | 40 A |

Architecture

| | |
|--------------|----|
| Type of pole | 1P |
| Curve | D |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical attributes

| | |
|---|-------|
| Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1 | 10 kA |
|---|-------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque | 2.80 - 2.80 Nm |

Voltage

| | |
|--|-------------|
| Rated operational voltage U _e | 230 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage U _i | 500 V |
| Rated impulse withstand voltage U _{imp} | 6000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |

Installation, mounting

| | |
|---|----------------|
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP20 |
| Grid distance | 60 mm |

Use conditions

| | |
|--|-------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Operating temperature | -25 - 70 °C |

Power

| | |
|---------------------------------------|--------|
| Total power loss under I _N | 3.71 W |
|---------------------------------------|--------|

Connectivity

| | |
|---|------------------|
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

Dimensions

| | |
|--------|----------|
| Height | 83 mm |
| Width | 17.50 mm |

Dimensions

| | |
|-------|-------|
| Depth | 70 mm |
|-------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|
