



ARM910U

MCB with dangerous arc detection 1M 10A B curve 6kA

Technical Features

Electric current

Rated current	10 A
Rated current -25°C	12.3 A
Rated current at -20°C	12.1 A
Rated current -15°C	11.9 A
Rated current -10°C	11.7 A
Rated current -5°C	11.5 A
Rated current at 0°C	11.3 A
Rated current 5°C	11.1 A
Rated current 10°C	10.8 A
Rated current 15°C	10.6 A
Rated current at 20°C	10.4 A
Rated current 25°C	10.2 A
Rated current 30°C	10 A
Rated current 35°C	9.8 A
Rated current at 40°C	9.6 A
Rated current at 45°C	9.4 A
Rated current at 50°C	9.2 A
Rated current 55°C	9 A
Rated current 60°C	8.7 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA

Architecture

Curve	B
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

Installation, mounting

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

Voltage

Rated insulation voltage Ui	400 V
Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 230 V

Power

Total power loss under IN	3.2 W
---------------------------	-------

Use conditions

Class of energy limitation I ² t	3
---	---

Endurance

Number of mechanical operations	8000
Electric endurance in number of cycles	2000

Installation, mounting

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	125 mm
Width	17.50 mm
Depth	70 mm

Use conditions	
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

Sustainability	
RoHS conform	Yes