



ARL932U

RCBO with dangerous arc detection 1M 32A B curve 6kA Type A 30mA LFL 1m

Technical Features

Electric current

Rated current	32 A
Rated current -25°C	38.6 A
Rated current at -20°C	38 A
Rated current -15°C	37.4 A
Rated current -10°C	36.8 A
Rated current -5°C	36.2 A
Rated current at 0°C	35.6 A
Rated current 5°C	35 A
Rated current 10°C	34.4 A
Rated current 15°C	33.8 A
Rated current at 20°C	33.2 A
Rated current 25°C	32.6 A
Rated current 30°C	32 A
Rated current 35°C	31.3 A
Rated current at 40°C	30.7 A
Rated current at 45°C	30 A
Rated current at 50°C	29.3 A
Rated current 55°C	28.6 A
Rated current 60°C	28 A
Rated current 65°C	27.3 A
Rated current 70°C	26.6 A
Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 61009-1	6 kA

Architecture

Curve	B
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	6 kA
---	------

Installation, mounting

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

Electric current

Breaking and opening capacity I _{dm}	3 kA
Rated residual operating current I _{dn}	30 mA

Voltage

Rated insulation voltage U _i	400 V
---	-------

Safety

Residual current type	A
-----------------------	---

Voltage

Rated impulse withstand voltage U _{imp}	4000 V
Rated operational voltage U _e	230 - 230 V

Power

Total power loss under I _N	12.5 W
---------------------------------------	--------

Use conditions

Class of energy limitation I ² t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

Endurance

Number of mechanical operations	8000
---------------------------------	------

Endurance

Electric endurance in number of cycles	2000
--	------

Capacity

Number of modules	1
-------------------	---

Installation, mounting

Type of bottom connection for modular devices	biconnect
---	-----------

Type of top connection for modular devices	Screw terminal
--	----------------

Dimensions

Height	125 mm
--------	--------

Width	17.50 mm
-------	----------

Depth	70 mm
-------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Sustainability

RoHS conform	Yes
--------------	-----