



ARL906U

**RCBO with dangerous arc detection 1M 6A B curve 6kA Type A 30mA LFL 1m**

**Technical Features**

**Electric current**

Rated current	6 A
Rated current -25°C	7.4 A
Rated current at -20°C	7.3 A
Rated current -15°C	7.1 A
Rated current -10°C	7 A
Rated current -5°C	6.9 A
Rated current at 0°C	6.8 A
Rated current 5°C	6.6 A
Rated current 10°C	6.5 A
Rated current 15°C	6.4 A
Rated current at 20°C	6.3 A
Rated current 25°C	6.1 A
Rated current 30°C	6 A
Rated current 35°C	5.9 A
Rated current at 40°C	5.7 A
Rated current at 45°C	5.6 A
Rated current at 50°C	5.5 A
Rated current 55°C	5.4 A
Rated current 60°C	5.2 A
Rated current 65°C	5.1 A
Rated current 70°C	5 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 61009-1	6 kA

**Architecture**

Curve	B
Type of pole	1P+N

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

**Electric current**

Breaking and opening capacity I <sub>dm</sub>	3 kA
Rated residual operating current I <sub>dn</sub>	30 mA

**Voltage**

Rated insulation voltage U <sub>i</sub>	400 V
---	-------

**Safety**

Residual current type	A
-----------------------	---

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

**Power**

Total power loss under I <sub>N</sub>	2.69 W
---------------------------------------	--------

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

**Endurance**

Number of mechanical operations	8000
---------------------------------	------

---

**Endurance**

---

Electric endurance in number of cycles	2000
--	------

---

**Capacity**

---

Number of modules	1
-------------------	---

---

**Installation, mounting**

---

Type of bottom connection for modular devices	biconnect
---	-----------

---

Type of top connection for modular devices	Screw terminal
--	----------------

---

**Dimensions**

---

Height	125 mm
--------	--------

---

Width	17.50 mm
-------	----------

---

Depth	70 mm
-------	-------

---

**Frequency**

---

Frequency	50 - 50 Hz
-----------	------------

---

**Sustainability**

---

RoHS conform	Yes
--------------	-----

---