



HMQ630FR

**Moulded Case Circuit Breaker h3+ PW1600 LI 3P3D 630A 50kA FTC**

**Technical Features**

**Electric current**

Rated current	630 A
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2	50 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	19.2 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	19.2 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in

**Tripping**

Response time when opening	12 ms
----------------------------	-------

**Electric current**

Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	30 kA
Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2	30 kA
Rated current 10°C according to IEC 60947	630 A
Rated current 15°C according to IEC 60947	630 A
Rated current 20°C according to IEC 60947	630 A
Rated current 25°C according to IEC 60947	630 A
Rated current 30°C according to IEC 60947	630 A
Rated current at 35°C according to IEC 60947	630 A
Rated current at 40°C according to IEC 60947	630 A
Rated current 45°C according to IEC 60947	630 A
Rated current 50°C according to IEC 60947	630 A
Rated current 55°C according to IEC 60947	630 A
Rated current at 60°C according to IEC 60947	630 A
Rated current 70°C according to IEC 60947	630 A
Rated current 65°C according to IEC 60947	630 A

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	50-50 Nm
Mounting-/Connection Position	Front

**Voltage**

Rated impulse withstand voltage Uimp	8 kV
Rated insulation voltage Ui	1000 V
Rated operational voltage Ue	220 - 690 V

**Functions**

Trip unit	Sentinel LI
-----------	-------------

**Power**

Total power loss under IN	13.4 W
Power loss per pole at In	1.8 W

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Equipment**

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Cover, door**

Interlockable	Yes
---------------	-----

**Cable**

Cable material	Copper Aluminium
----------------	---------------------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

**Dimensions**

Height	330 mm
Width	210 mm
Depth	198 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Compatibility**

Suitable for DIN Rail	No
Compatible with RDC AOB	No

**Power supply**

Position power supply	Bidirectional
-----------------------	---------------

**Connectivity**

Type of connection	Bolt connection
--------------------	-----------------

**Electrical protection**

Long-time overload protection (ltd): delay (tr)	0.5 s 1 s 2 s 4 s 5 s 8 s 10 s 15 s 20 s 25 s
---	--

Instantaneous protection (ii): dial setting coefficient	1.5 2 3 4 6 8 10 12 15
---	--

**Sustainability**

RoHS conform	Yes
--------------	-----