# Product Datasheet
NCN303A



NCN303A

**MCB 3P 10kA/15kA C-3A 3M**

## Technical Features

| Electric current | |
|---|---|
| Rated current | 3 A |
| Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 15 kA |
| Rated current -15°C | 3.47 A |
| Rated current -10°C | 3.42 A |
| Rated current -5°C | 3.37 A |
| Rated current at 0°C | 3.32 A |
| Rated current 5°C | 3.27 A |
| Rated current 10°C | 3.22 A |
| Rated current 15°C | 3.17 A |
| Rated current at 20°C | 3.11 A |
| Rated current 25°C | 3.06 A |
| Rated current 30°C | 3 A |
| Rated current 35°C | 2.93 A |
| Rated current at 40°C | 2.85 A |
| Rated current at 45°C | 2.77 A |
| Rated current at 50°C | 2.69 A |
| Rated current 55°C | 2.60 A |
| Rated current 60°C | 2.52 A |
| Rated current 65°C | 2.43 A |
| Rated current 70°C | 2.33 A |

| Architecture | |
|---|---|
| Type of pole | 3P |
| Curve | C |

| Capacity | |
|---|---|
| Number of modules | 3 |

| Main electrical attributes | |
|---|---|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 10 kA |

| Installation, mounting | |
|---|---|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque | 2.80 - 2.80 Nm |

| Voltage | |
|---|---|
| Rated operational voltage Ue | 400 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 6000 V |

| Frequency | |
|---|---|
| Frequency | 50 - 60 Hz |

| Connection | |
|---|---|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 $mm^2$ |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 $mm^2$ |
| Cross-section of input with screws, for flexible conductors | 1 - 25 $mm^2$ |
| Cross-section of input with screws, for massive conductors | 1 - 35 $mm^2$ |

| Installation, mounting | |
|---|---|
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

| | |
|---|---|
| **Safety** | |
| Ingress Protection (IP) class | IP20 |
| Grid distance | 60 mm |
| **Use conditions** | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation $I^2t$ | 3 |
| Operating temperature | -25 - 70 °C |
| **Power** | |
| Total power loss under IN | 6.60 W |
| **Connectivity** | |
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |
| **Dimensions** | |
| Height | 83 mm |
| Width | 52.50 mm |
| Depth | 70 mm |
| **Sustainability** | |
| RoHS conform | Yes |