



HW1M312DB

**ACB HW1 55kA 1250A 3P Drawout TU sentinel LSI, VCVC**

**Technical Features**

**Electric current**

Rated current	1250 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 400 V AC IEC 60947-2	55 kA
Rated service breaking capacity $I_{cs}$ under 230 V AC according to IEC 60947-2	55 kA
Rated service breaking capacity $I_{cs}$ under 400 V AC according to IEC 60947-2	55 kA

**Endurance**

Electric endurance in number of cycles	6000
Number of mechanical operations	25000

**Voltage**

Rated insulation voltage $U_i$	1000 V
Rated impulse withstand voltage $U_{imp}$	12000 V
Type voltage supply	AC

**Resistance**

Internal resistance	50 $\mu\Omega$
---------------------	----------------

**Architecture**

Number of poles	3
Number of protected poles	3
Device construction type	Drawout
Type of pole	3P3D

**Tripping**

Time of response when closing	45 ms
-------------------------------	-------

**Power**

Total power loss under IN	187.40 W
---------------------------	----------