



L71M

Fuse-switch-disconnector D02 E18 63A AC400 V 1pole DIN rail

Technical Features

Fuse

Fuse size	D02
-----------	-----

Architecture

Number of poles	1
-----------------	---

Electric current

Rated current	63 A
Rated current of fuse cartridge	2 A 4 A 6 A 10 A 16 A 20 A 25 A 32 A 35 A 40 A 50 A 63 A

Installation, mounting

Mounting on	DIN rail
Nominal tightening torque	3.30 - 3.30 Nm

Dimensions

Height	85 mm
Width	27 mm
Depth	79 mm

Connection

Cross-section flexible conductor	1.5 - 35 mm ²
----------------------------------	--------------------------

Use conditions

Operating temperature	-25 - 40 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Total power loss under IN	1.60 W
---------------------------	--------

Connection

Cross-section rigid conductor	1.5 - 35 mm ²
-------------------------------	--------------------------

Power

Power loss of the Fuse-Link installed in device	5.50 W
---	--------

Texts

Protection	Contact protection safe from touch by finger and back of hand
------------	---

Electric current

Rated conditional short-circuit current I _{cc}	50 kA
---	-------

Voltage

Rated insulation voltage U _i	800 V
---	-------

Safety

Ingress Protection (IP) class	IP20C
-------------------------------	-------

Materials

Material	Plastic
----------	---------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes