



NCN402A

### MCB 4P 10kA/15kA C-2A 4M

#### Technical Features

##### Electric current

Rated current	2 A
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	15 kA
Rated current -25°C	2.59 A
Rated current at -20°C	2.54 A
Rated current -15°C	2.50 A
Rated current -10°C	2.45 A
Rated current -5°C	2.39 A
Rated current at 0°C	2.34 A
Rated current 5°C	2.29 A
Rated current 10°C	2.23 A
Rated current 15°C	2.18 A
Rated current at 20°C	2.12 A
Rated current 25°C	2.06 A
Rated current 30°C	2 A
Rated current 35°C	1.93 A
Rated current at 40°C	1.85 A
Rated current at 45°C	1.77 A
Rated current at 50°C	1.69 A
Rated current 55°C	1.61 A
Rated current 60°C	1.51 A
Rated current 65°C	1.42 A
Rated current 70°C	1.31 A

##### Architecture

Type of pole	4P
Curve	C

##### Capacity

Number of modules	4
-------------------	---

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for massive conductors	1 - 35 mm²

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

# Product Datasheet

## NCN402A

---

### Safety

Ingress Protection (IP) class	IP20
Grid distance	60 mm

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	8.63 W
---------------------------	--------

### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	70 mm
Depth	70 mm

### Sustainability

RoHS conform	Yes
--------------	-----