



WNA100B



IP55

Soc.out. insert earth.pin+hinged cover surf./flushmtd,enhncd contact prot.,W1,wh

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current IN 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

RAL code Similar to RAL 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Contains recycled material (% of total plastic weight) 0 %

Dimensions

Height 71 mm

Width 71 mm

Depth 22.80 mm

Number of units 1

Built-in depth flush-mounted boxes 0 mm

Built-in depth 22 mm

Connection

Connector/plug type Turn screw lock

Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm²

Installation, mounting

Mounting on Flush mounting
Surface mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Plug-in connection

With claw mounting No

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Pre-equipped with Socket outlet

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP55
Usable in higher IP class	IP55 with closed cover

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals
Labelling	Without labelling

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes