



WNA105B



IP55

sock.outl. insert w. earth.pin a. hing. cov. SM/flush-mounted, cont.prot., W.1

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Pure white

RAL code 9010

Surface finish Matt

Material Polycarbonate (PC)
Polypropylene (PP)

Treatment Untreated

Contains recycled material (% of total plastic weight) 0 %

Dimensions

Height 75 mm

Width 75 mm

Depth 22.80 mm

Number of units 1

Built-in depth flush-mounted boxes 35 mm

Built-in depth 22 mm

Height of P-touch band for labelling field 12 mm

Connection

Connector/plug type Turn screw lock

Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm²

Installation, mounting

Mounting on Flush mounting
Surface mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Plug-in connection

With claw mounting No

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Pre-equipped with Socket outlet

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
----------------------------------	-----

Impact resistance IK	IK08
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Identification

With imprint	No
--------------	----

Texts

Imprint	Without imprint
---------	-----------------

Cover	For covering of socket outlets
-------	--------------------------------

Protection	Without protective screen
------------	---------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	Without labelling
-----------	-------------------

Suitable for

cubyko	
--------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----
